6305438 - BISON EPOXY UNIVERSAL BLISTER 24 ML MULTI LANGUAGE



PLUS ENDFEST UNIVERSAL STRONG DUAL-COMPONENT EPOXY ADHESIVE



PRODUCT DESCRIPTION

Universal strong dual-component epoxy adhesive for repairing metal, pottery, porcelain, glass, pearls, precious stones and various synthetics. Temperature resistant, water resistant, chemical resistant and paintable.

FIELD OF APPLICATION

Suitable for repairs to metal, ceramics, porcelain, crystal, glass, pearls, precious stones and various synthetics (polyester, bakelite, formica, rigid polystyrene and acrylic glass (Perspex®).

Not suitable for Polyethylene (PE), polypropylene (PP), PTFE and silicone rubber.

PROPERTIES

- · Super-strong (up to 170 kg/cm²)
- · Resistant to temperatures between -40 °C and +100 °C
- · Filling
- · Water resistant
- · Chemical resistant

· Paintable

PREPARATION

Working Conditions: Only apply at temperatures between +10 °C and +35 °C. Product cures by mixing the resin and the hardener.

Personal safety: Preferably wear gloves.

Surface Requirements: The surface must be dry, clean and free of dust and grease.

Preliminary Surface Treatment: Degrease parts to be bonded with methylated spirit. Roughen smooth surfaces (sandpaper). **Tools:** Mix the components by means of the supplied mixing bowl and spatula.

APPLICATION

Coverage: $1 \text{ ml} = \text{approx } 10 \text{ cm}^2 \text{ at a film thickness of } 1 \text{ mm}$ **Directions for use:**

Remove the spatula from the side of the double syringe, and the closure cap from the handle. Break the seal of the double syringe.

Press out an equal amount of both components onto the enclosed mixing tray. Mix these two equal parts well with a spatula until a mixture is obtained with a homogeneous colour. Apply the mixture, which at room temperature (+20 °C) remains toolable for about 1.5 hours, as a thin layer on one of the two materials. Join the materials and keep them in place for 7 hours. Be careful not to move the parts before the adhesive has cured. Resin and hardener must not come into contact with each other unless for usage.

Stains/residue: Remove wet stains immediately with warm water and soap. Cured adhesive residue can only be removed mechanically.

Advice: Some types of synthetics can not be joined such as polyethylene and polypropylene. Use a piece of adhesive tape in order to keep the parts in place while the adhesive is curing. **Points of attention:** After use close well (note: always place back the cap in the same way, due to the bonding of the cap to the double syringe). For optimum performance it is important to create a larger amount of adhesive and mix it very well. Curing time depends on the temperature. Adhesive does not cure below +5 °C.

Our advice is based on extensive research and practical experience. However, in view of the large variety of materials and the conditions under which our products are applied, we assume no responsibility for the results obtained and/or any damage caused by the use of the product. Nevertheless, our Service Department is always at your disposal for any advice needed.

6305438 - BISON EPOXY UNIVERSAL BLISTER 24 ML MULTI LANGUAGE



PLUS ENDFEST UNIVERSAL STRONG DUAL-COMPONENT EPOXY ADHESIVE

TECHNICAL SPECIFICATIONS

Epoxy resin Water, oil, grease, solvents, Jiluted acids and alkalis Dpaque, honey coloured iquid I,1 g/cm ³ Very good
liluted acids and alkalis Dpaque, honey coloured iquid 1,1 g/cm ³ /ery good
iquid 1,1 g/cm ³ /ery good
,1 g/cm ³ /ery good
/ery good
7.4
9 N/mm ²
24 hours
ó hours
40 °C
00 °C
Good
:1
les
90 minutes
/es
/ery good
Aedium viscosity
35000 mPa·s
Good

PACK SIZES

24ml/25g

STORAGE CONDITIONS

Store in tightly closed packaging in a dry, cool and frost-free place.

Our advice is based on extensive research and practical experience. However, in view of the large variety of materials and the conditions under which our products are applied, we assume no responsibility for the results obtained and/or any damage caused by the use of the product. Nevertheless, our Service Department is always at your disposal for any advice needed.